



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F040841ECO 40W T8 60" 41K 82cri *Sylvania-Ledvance*

Catalog Number	F040841ECO
Manufacturer	Sylvania-Ledvance
Description	40W, 60" Mol, T8 Octron Fluorescent Lamp, 4100K Color Temperature, Rare Earth Phosphor, 82 Cri, Suitable For Is or RS Operation, Ecologic
Weight per unit	0.5300 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
average life	30000
Base	Medium Bipin
bulb type	T8
Lamp Type	RAPID & INSTANT START
Shape	T8
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	40

Material, Color, and Finish

color rendering index (cri)	82
color temperature	4100
Finish	Phosphor Coated

Dimensions and Weight

Diameter	1
----------	---

Descriptions

Description	40W T8 60" 41K 82CRI
extra long description	SYL FO40841ECO/22146 FO40841ECO 30/
Long Description	40W, 60" MOL, T8 OCTRON fluorescent lamp, 4100K color temperature, rare earth phosphor, 82 CRI, suitable for IS or RS operation, ECOLOGIC
Product Type	FO40841ECO 30/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135221460
Manufacturers Part Number	FO40/841/ECO/22146
UPC	046135221460



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description Fluorescent

Type FLUORESCENT

Packaging

Carton 1

Package 30

Weight Per each 0.53

Uses, Certifications, and Standards

Application Commercial/Residential