



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## F096835HOECO #22206

*Sylvania-Ledvance*

Catalog Number	F096835HOECO
Manufacturer	Sylvania-Ledvance
Description	86W, 96" Mol, T8 Octron High Output Fluorescent Lamp, 3500K Color Temperature, Rare Earth Phosphor, 85 Cri, Suitable For RS Operation, Ecologic
Weight per unit	0.9200 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

amperage rating	Ballast Dependent
average life	18000
Base	Recessed Double Contact
Lamp Type	RAPID & INSTANT START
Shape	T8
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	86

### Material, Color, and Finish

color rendering index (cri)	85
color temperature	3500
Finish	Phosphor Coated

### Dimensions and Weight

Diameter	1
----------	---

### Descriptions

Description	#22206
extra long description	SYL FO96/835/HO/ECO/22206 FO96835HO
Long Description	86W, 96" MOL, T8 OCTRON high output fluorescent lamp, 3500K color temperature, rare earth phosphor, 85 CRI, suitable for RS operation, ECOLOGIC
Product Type	FO96835HOECO 24/CS 1/Sku

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135222061
Manufacturers Part Number	FO96/835/HO/ECO/22206
UPC	046135222061

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	24
Weight Per each	0.92

## Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------