



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F096835HOECO #22206

Sylvania-Ledvance

Catalog Number	F096835HOECO
Manufacturer	Sylvania-Ledvance
Description	86W, 96" Mol, T8 Octron High Output Fluorescent Lamp, 3500K Color Temperature, Rare Earth Phosphor, 85 Cri, Suitable For RS Operation, Ecologic
Weight per unit	0.9200 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
average life	18000
Base	Recessed Double Contact
Lamp Type	RAPID & INSTANT START
Shape	T8
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	86

Material, Color, and Finish

color rendering index (cri)	85
color temperature	3500
Finish	Phosphor Coated

Dimensions and Weight

Diameter	1
----------	---

Descriptions

Description	#22206
extra long description	SYL FO96/835/HO/ECO/22206 FO96835HO
Long Description	86W, 96" MOL, T8 OCTRON high output fluorescent lamp, 3500K color temperature, rare earth phosphor, 85 CRI, suitable for RS operation, ECOLOGIC
Product Type	FO96835HOECO 24/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135222061
Manufacturers Part Number	FO96/835/HO/ECO/22206
UPC	046135222061

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	24
Weight Per each	0.92

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------