



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F096841HOECO 86W T8 96" 41K 85 Cri RS Op

Sylvania-Ledvance

Catalog Number	F096841HOECO
Manufacturer	Sylvania-Ledvance
Description	86W, 96" Mol, T8 Octron High Output Fluorescent Lamp, 4100K Color Temperature, Rare Earth Phosphor, 85 Cri, Suitable For RS Operation, Ecologic
Weight per unit	0.9200 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
average life	18000
Base	Recessed Double Contact
bulb type	T8
Lamp Type	RAPID & INSTANT START
Shape	T8
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	86

Material, Color, and Finish

color rendering index (cri)	85
color temperature	4100
Finish	Phosphor Coated

Dimensions and Weight

Diameter	1
----------	---

Descriptions

Description	86W T8 96" 41K 85 CRI RS OP
extra long description	SYL F096841HOECO/22207 F096841HOECO
Long Description	86W, 96" MOL, T8 OCTRON high output fluorescent lamp, 4100K color temperature, rare earth phosphor, 85 CRI, suitable for RS operation, ECOLOGIC
Product Type	F096841HOECO 24/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135222078
Manufacturers Part Number	FO96/841/HO/ECO/22207
UPC	046135222078



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description Fluorescent

Type FLUORESCENT

Packaging

Carton 1

Package 24

Weight Per each 0.92

Uses, Certifications, and Standards

Application Commercial/Residential