



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## F20T12DECO 20W T12 24" Daylight 76 Cri Bi-Pin Fluor Lamp

*Ge By Current Lamps*

Catalog Number	F20T12DECO
Manufacturer	Ge By Current Lamps
Description	Ge Ecolux®, 20 WTT, 1025 LM, 6500 KV, 75 Cri, 1.5 In Diameter, 24 In Length, Medium Bi-Pin (G13) Base, 9000 HR Average Life
Weight per unit	0.3700 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

average life	9000.0
Base	Medium Bi-Pin (G13)
lumens	1025.0
Wattage	20.0

### Material, Color, and Finish

color rendering index (cri)	75.0
color temperature	6500.0

### Dimensions and Weight

Diameter	1.5
Length	24.0

### Descriptions

Description	20W T12 24" DAYLIGHT 76 CRI BI-PIN FLUOR LAMP
extra long description	GEL F20T12/D/ECO 80047 SLIM LINE /
Long Description	GE Ecolux®, 20 WTT, 1025 LM, 6500 KV, 75 CRI, 1.5 IN Diameter, 24 IN Length, Medium Bi-Pin (G13) Base, 9000 HR Average Life
Product Type	80047 Slim Line / F20

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168800471
Manufacturers Part Number	F20T12/D/ECO
UPC	043168800471

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

### Packaging

Carton	1
Package	24
Weight Per each	0.37

### Uses, Certifications, and Standards

Application	Full Wattage
-------------	--------------