



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F25T8SP30ECO 25W T8 36" 3000K 78 Cri Bi-Pin Energy Saving

Ge By Current Lamps

Catalog Number	F25T8SP30ECO
Manufacturer	Ge By Current Lamps
Description	Ge Ecolux®, 25 WTT, 2080 LM, 3000 KV, 78 Cri, 1 In Diameter, 35.78 In Length, Medium Bi-Pin (G13) Base, 30000 HR Average Life
Weight per unit	0.3500 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

average life	30000.0
Base	Medium Bi-Pin (G13)
lumens	2080.0
Wattage	25.0

Material, Color, and Finish

color rendering index (cri)	78.0
color temperature	3000.0

Dimensions and Weight

Diameter	1.0
Length	35.78

Descriptions

Description	25W T8 36" 3000K 78 CRI BI-PIN ENERGY SAVING
extra long description	GEL F25T8/SP30/ECO 45750 FLUORESCEN
Long Description	GE Ecolux®, 25 WTT, 2080 LM, 3000 KV, 78 CRI, 1 IN Diameter, 35.78 IN Length, Medium Bi-Pin (G13) Base, 30000 HR Average Life
Product Type	45750 Fluorescent

Manufacturer Information

Brand	GE Current, a Daintree company
GTIN	00043168457507
Manufacturers Part Number	F25T8/SP30/ECO
UPC	043168457507

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Packaging

Carton	1
Weight Per each	0.35

Uses, Certifications, and Standards

Application	Full Wattage
-------------	--------------