



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F26DBX835ECO 26W 2 Pin Twin Tube Biax G24D-3 3500K Compact

Ge By Current Lamps

Catalog Number	F26DBX835ECO
Manufacturer	Ge By Current Lamps
Description	Ge Ecolux®, 26 WTT, 105 V, 1710 LM, 3500 KV, 82 Cri, 6.67 In Length, G24D-3 Base, 10000 HR Average Life
Weight per unit	0.2000 (lbs/each)
Product Category	Integrated Non-Ballasted Lamps

Features

average life	10000
Base	G24d-3
lumens	1710
Voltage Rating	105
Wattage	26

Material, Color, and Finish

color rendering index (cri)	82.0
color temperature	3500

Dimensions and Weight

Length	6.67
--------	------

Descriptions

Description	26W 2 PIN TWIN TUBE BIAX G24D-3 3500K COMPACT
extra long description	GEL F26DBX/835/ECO 97608 PLUG IN CF
Long Description	GE Ecolux®, 26 WTT, 105 V, 1710 LM, 3500 KV, 82 CRI, 6.67 IN Length, G24d-3 Base, 10000 HR Average Life
Product Type	97608 Plug In CFL

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168976084
Manufacturers Part Number	F26DBX/835/ECO
UPC	043168976084

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Packaging

Carton	1
Package	10
Weight Per each	0.2