



# F28T8/841/ES



**Description** 28W Energy Saving Universal Start 4100K 85 CRI Medium Bi-pin

**Ordering Code** 06605

**UNSPSC Code** 39101605

## Specifications

<b>Watts</b>	28
<b>Base Type</b>	G13
<b>Bulb Type</b>	T-8
<b>MOL in/mm</b>	48.0/1219
<b>Length</b>	4'
<b>MOD in/mm</b>	1.0/26
<b>Approx Initial Lumens</b>	2800
<b>Approx Mean Lumens</b>	2635
<b>CT deg K</b>	4100
<b>CRI</b>	85
<b>Avg Life 3 HR Inst Start</b>	24,000
<b>Avg Life 12 HR Prog Start</b>	30,000
<b>Special Desc</b>	Three Phosphor, Universal Start

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975  
Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335



# F28T8/841/ES



<b>Description</b>	28W Energy Saving Universal Start 4100K 85 CRI Medium Bi-pin
<b>Ordering Code</b>	06605
<b>UNSPSC Code</b>	39101605

## Specifications

<b>Watts</b>	28
<b>Base Type</b>	G13
<b>Bulb Type</b>	T-8
<b>MOL in/mm</b>	48.0/1219
<b>Length</b>	4'
<b>MOD in/mm</b>	1.0/26
<b>Approx Initial Lumens</b>	2800
<b>Approx Mean Lumens</b>	2635
<b>CT deg K</b>	4100
<b>CRI</b>	85
<b>Avg Life 3 HR Inst Start</b>	24,000
<b>Avg Life 12 HR Prog Start</b>	30,000
<b>Special Desc</b>	Three Phosphor, Universal Start

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335