




GE  
Lighting

**66471 - F28T8/XL/SPP35/ECO**

F28T8/XLSPP35ECO-T8-SPP NEW TECHNICAL LAMPS

• Meets TCLP requirements



**GENERAL CHARACTERISTICS**

Lamp Type	Linear Fluorescent - Straight
	Linear
Bulb	T8
Base	Medium Bi-Pin (G13)
Rated Life (NOM)	40000.0 h
Rated Life (instant start) @ Time	20000 h @ 3 h
	28000 h @ 12 h
Rated Life (rapid start) @ Time	40000.0 @ 3.0/45000.0 @ 12.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	15.0 °C
Mercury Content (NOM)	2.95 mg
Picograms of Mercury (NOM)	30.22541 pg
Primary Application	Energy Saving

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens (NOM)	2600.0
Mean Lumens (NOM)	2440.0
Nominal Initial Lumens per Watt (NOM)	92.85714
Color Temperature (NOM)	3500.0 K
Color Rendering Index (CRI) (NOM)	80.0

**ELECTRICAL CHARACTERISTICS**

Wattage (NOM)	28.0
---------------	------

**DIMENSIONS**

Maximum Overall Length (MOL) (NOM)	48.000 in(1219.2 mm)
Nominal Length (NOM)	48.000 in(1219.2 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

**PRODUCT INFORMATION**

Product Code	66471
Description	F28T8/XL/SPP35/ECO
Standard Package	Case
Standard Package GTIN	10043168664711
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
UPC	043168664714




GE  
Lighting

**66471 - F28T8/XL/SPP35/ECO**

F28T8/XLSPP35ECO-T8-SPP NEW TECHNICAL LAMPS

• Meets TCLP requirements



**GENERAL CHARACTERISTICS**

Lamp Type	Linear Fluorescent - Straight Linear
Bulb	T8
Base	Medium Bi-Pin (G13)
Rated Life (NOM)	40000.0 h
Rated Life (instant start) @ Time	20000 h @ 3 h
Rated Life (rapid start) @ Time	28000 h @ 12 h
	40000.0 @ 3.0/45000.0 @ 12.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	15.0 °C
Mercury Content (NOM)	2.95 mg
Picograms of Mercury (NOM)	30.22541 pg
Primary Application	Energy Saving

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens (NOM)	2600.0
Mean Lumens (NOM)	2440.0
Nominal Initial Lumens per Watt (NOM)	92.85714
Color Temperature (NOM)	3500.0 K
Color Rendering Index (CRI) (NOM)	80.0

**ELECTRICAL CHARACTERISTICS**

Wattage (NOM)	28.0
---------------	------

**DIMENSIONS**

Maximum Overall Length (MOL) (NOM)	48.000 in(1219.2 mm)
Nominal Length (NOM)	48.000 in(1219.2 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

**PRODUCT INFORMATION**

Product Code	66471
Description	F28T8/XL/SPP35/ECO
Standard Package	Case
Standard Package GTIN	10043168664711
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
UPC	043168664714