



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## F30T12CWRS 30W T12 36" Cool White 60 Cri Bi-Pin Rapid Start

*Sylvania-Ledvance*

Catalog Number	F30T12CWRS
Manufacturer	Sylvania-Ledvance
Description	30W, T12 Rapid Start Fluorescent Lamp, Cool White Phosphor, 4200K Color Temperature, 60 Cri, 18000 Avg Rated Life At 3 HRS/Start
Weight per unit	0.6600 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

amperage rating	Ballast Dependent
average life	18000
Base	Medium Bipin
Lamp Type	RAPID START
lumens	2200 Initial Lumens at 25 Degrees C
Shape	T12
start type	Rapid Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	30

### Material, Color, and Finish

color rendering index (cri)	60
color temperature	4200
Finish	Phosphor Coated

### Dimensions and Weight

Diameter	1.5 in
----------	--------

### Descriptions

Description	30W T12 36" COOL WHITE 60 CRI BI-PIN RAPID START
extra long description	SYL F30T12/CW/RS/23476 F30T12CWRS 3
Long Description	30W, T12 rapid start fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI, 18000 Avg rated life at 3 hrs/start
Product Type	F30T12CWRS 30/CS 1/Sku
Special Features	COOL WHITE

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135234767
Manufacturers Part Number	F30T12/CW/RS/23476
UPC	046135234767



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... Fluorescent

Type ..... FLUORESCENT

## Packaging

Carton ..... 1

Package ..... 30

Weight Per each ..... 0.66

## Uses, Certifications, and Standards

Application ..... Commercial/Residential