



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F30T12CWRSECO *Delisted* 30W T12 36" CW 60 Cri Bi-Pin Rapid STRT

Ge By Current Lamps

Catalog Number	F30T12CWRSECO
Manufacturer	Ge By Current Lamps
Description	Linear Fluorescent Lamp, G13 Medium Bi-Pin Base, T12 Bulb Shape, 60, 18000 H Average Life, 4100 K, Cool White, 30 W, 2200 LM Brightness (Lumens), Soda Lime Housing Material, 1.5 In Diameter, 36.0 In Length, Rapid, 1.86 LB
Weight per unit	0.5200 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

Base	Medium Bi-Pin (G13)
lumens	2200.0

Material, Color, and Finish

color rendering index (cri)	60.0
-----------------------------	------

Dimensions and Weight

Diameter	1.5
----------	-----

Descriptions

Description	*DELISTED* 30W T12 36" CW 60 CRI BI-PIN RAPID STRT
-------------	--

Manufacturer Information

Brand	GE Current
GTIN	00043168800846
UPC	043168800846

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Package	24
Weight Per each	0.52