



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **F30T12CWRSECO \*Delisted\* 30W T12 36" CW 60 Cri Bi-Pin Rapid STRT**

*Ge By Current Lamps*

Catalog Number	F30T12CWRSECO
Manufacturer	Ge By Current Lamps
Description	Linear Fluorescent Lamp, G13 Medium Bi-Pin Base, T12 Bulb Shape, 60, 18000 H Average Life, 4100 K, Cool White, 30 W, 2200 LM Brightness (Lumens), Soda Lime Housing Material, 1.5 In Diameter, 36.0 In Length, Rapid, 1.86 LB
Weight per unit	0.5200 (lbs/each)
Product Category	Linear Fluorescent Straight La

### **Features**

Base	Medium Bi-Pin (G13)
lumens	2200.0

### **Material, Color, and Finish**

color rendering index (cri)	60.0
-----------------------------	------

### **Dimensions and Weight**

Diameter	1.5
----------	-----

### **Descriptions**

Description	*DELISTED* 30W T12 36" CW 60 CRI BI-PIN RAPID STRT
extra long description	GEL F30T12/CW/RS/ECO 80084 FLUORESC

### **Manufacturer Information**

Brand	GE Current
GTIN	00043168800846
UPC	043168800846

### **Taxonomies, Classifications, and Categories**

Category Description	Fluorescent
----------------------	-------------

### **Packaging**

Carton	1
Package	24
Weight Per each	0.52