



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F30T8CW 30W T8 36" Cool White 62 Cri Bi-Pin Fluorescent *Sylvania-Ledvance*

Catalog Number	F30T8CW
Manufacturer	Sylvania-Ledvance
Description	30W, T8 Preheat Fluorescent Lamp, Cool White Phosphor, 4200K Color Temperature, 60 Cri. 7500 Avg Rated Life At 3 HRS/Start
Weight per unit	0.3300 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Medium Bipin
Lamp Type	PREHEAT
lumens	2,180
Shape	T8
start type	PREHEAT
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	30

Material, Color, and Finish

color rendering index (cri)	60
color temperature	4200

Descriptions

Description	30W T8 36" COOL WHITE 62 CRI BI-PIN FLUORESCENT
extra long description	SYL F30T8CW/23116 F30T8CW 24/CS 1/S
Long Description	30W, T8 preheat fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI. 7500 Avg rated life at 3 hrs/start
Special Features	COOL WHITE

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135231162
Manufacturers Part Number	F30T8/CW/23116
UPC	046135231162

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	24
Weight Per each	0.33

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------