



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F32T8SPP50ECO 32W T8 48" 5000K 80 Cri *Ge By Current Lamps*

Catalog Number	F32T8SPP50ECO
Manufacturer	Ge By Current Lamps
Description	Linear Fluorescent Lamp, Pin/Plug-In G13 Base, T8 Bulb Shape, 80, 30000 H Average Life, 5000 K, 32 W, 2900 LM Brightness (Lumens), Soda Lime Glass Housing Material, 1.0 In Diameter, 48.0 In Length, Instant;Rapid, +10 °C Operating Temperature, 0.55 LB/Ea
Weight per unit	0.5600 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

Base	Medium Bi-Pin (G13)
lumens	2900.0
Wattage	32.0

Material, Color, and Finish

color rendering index (cri)	80.0
-----------------------------	------

Dimensions and Weight

Length	48.0
--------	------

Descriptions

Description	32W T8 48" 5000K 80 CRI
-------------	-------------------------

Manufacturer Information

Brand	GE Current
GTIN	00043168663502
UPC	043168663502

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Availability

Manufacturer Status	Inactive
minimum qty	36

Packaging

Carton	1
Package	36
Weight Per each	0.56