



GE
Lighting

68850 - F32T8/SPX30/ECO2
F32T8/SPX30/ECO2



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight
Bulb	Linear
Base	T8
Rated Life (NOM)	Medium Bi-Pin (G13)
Rated Life (instant start) @ Time	30000.0 h
Rated Life (rapid start) @ Time	21000 h @ 3 h
	30000 h @ 12 h
	30000.0 @ 3.0/36000.0 @ 12.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	10.0 °C
Mercury Content (NOM)	2.95 mg
Picograms of Mercury (NOM)	35.4994 pg
Primary Application	Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	2925.0
Mean Lumens (NOM)	2770.0
Nominal Initial Lumens per Watt (NOM)	91.40625
Color Temperature (NOM)	3000.0 K
Color Rendering Index (CRI) (NOM)	85.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	32.0
---------------	------

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	48.000 in(1219.2 mm)
Nominal Length (NOM)	48.000 in(1219.2 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)


PRODUCT INFORMATION

Product Code	68850
Description	F32T8/SPX30/ECO2
Standard Package	Case
Standard Package GTIN	10043168688502
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	36
UPC	043168688505



GE
Lighting

68850 - F32T8/SPX30/ECO2
F32T8/SPX30/ECO2



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight
Bulb	Linear
Base	T8
Rated Life (NOM)	Medium Bi-Pin (G13)
Rated Life (instant start) @ Time	30000.0 h
Rated Life (rapid start) @ Time	21000 h @ 3 h
	30000 h @ 12 h
	30000.0 @ 3.0/36000.0 @ 12.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	10.0 °C
Mercury Content (NOM)	2.95 mg
Picograms of Mercury (NOM)	35.4994 pg
Primary Application	Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	2925.0
Mean Lumens (NOM)	2770.0
Nominal Initial Lumens per Watt (NOM)	91.40625
Color Temperature (NOM)	3000.0 K
Color Rendering Index (CRI) (NOM)	85.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	32.0
---------------	------

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	48.000 in(1219.2 mm)
Nominal Length (NOM)	48.000 in(1219.2 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

PRODUCT INFORMATION

Product Code	68850
Description	F32T8/SPX30/ECO2
Standard Package	Case
Standard Package GTIN	10043168688502
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	36
UPC	043168688505