



GE
Lighting

66342 - F32T8/SPX65/ECO2

F32 T8 6500K Product Line Extension



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight Linear
Bulb	T8
Base	Medium Bi-Pin (G13)
Rated Life (NOM)	30000.0 h
Rated Life (instant start) @ Time	21000 h @ 3 h
Rated Life (rapid start) @ Time	30000 h @ 12 h
	30000.0 @ 3.0/36000.0 @ 12.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	10.0 °C
Mercury Content (NOM)	2.95 mg
Picograms of Mercury (NOM)	35.69268 pg
Primary Application	Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	2900.0
Mean Lumens (NOM)	2755.0
Nominal Initial Lumens per Watt (NOM)	90.625
Color Temperature (NOM)	6500.0 K
Color Rendering Index (CRI) (NOM)	78.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	32.0
---------------	------

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	48.000 in(1219.2 mm)
Nominal Length (NOM)	48.000 in(1219.2 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

PRODUCT INFORMATION


Product Code	66342
Description	F32T8/SPX65/ECO2
Standard Package	Case
Standard Package GTIN	10043168663424
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
UPC	043168663427



GE
Lighting

66342 - F32T8/SPX65/ECO2

F32 T8 6500K Product Line Extension



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight Linear
Bulb	T8
Base	Medium Bi-Pin (G13)
Rated Life (NOM)	30000.0 h
Rated Life (instant start) @ Time	21000 h @ 3 h
Rated Life (rapid start) @ Time	30000 h @ 12 h
	30000.0 @ 3.0/36000.0 @ 12.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	10.0 °C
Mercury Content (NOM)	2.95 mg
Picograms of Mercury (NOM)	35.69268 pg
Primary Application	Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	2900.0
Mean Lumens (NOM)	2755.0
Nominal Initial Lumens per Watt (NOM)	90.625
Color Temperature (NOM)	6500.0 K
Color Rendering Index (CRI) (NOM)	78.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	32.0
---------------	------

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	48.000 in(1219.2 mm)
Nominal Length (NOM)	48.000 in(1219.2 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

PRODUCT INFORMATION

Product Code	66342
Description	F32T8/SPX65/ECO2
Standard Package	Case
Standard Package GTIN	10043168663424
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
UPC	043168663427