



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F4030BXSPX35 40W 4 Pin Twin Tube Biax 2G11 3500K Compact Fluor

Ge By Current Lamps

Catalog Number	F4030BXSPX35
Manufacturer	Ge By Current Lamps
Description	Ge, 40 WTT, 126 V, 3150 LM, 3500 KV, 82 Cri, 22.5 In Length, 4-Pin (2G11) Base, 20000 HR Average Life
Weight per unit	0.6900 (lbs/each)
Product Category	Integrated Non-Ballasted Lamps

Features

average life	20000
Base	2G11 (4-pins)
lumens	3150
Voltage Rating	126
Wattage	40

Material, Color, and Finish

color rendering index (cri)	82.0
color temperature	3500

Dimensions and Weight

Length	22.5
--------	------

Descriptions

Description	40W 4 PIN TWIN TUBE BIAx 2G11 3500K COMPACT FLUOR
extra long description	GEL F40/30BX/SPX35 16648 CFL DEVICE
Long Description	GE, 40 WTT, 126 V, 3150 LM, 3500 KV, 82 CRI, 22.5 IN Length, 4-Pin (2G11) Base, 20000 HR Average Life
Product Type	16648 CFL Devices

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168166485
Manufacturers Part Number	F40/30BX/SPX35
UPC	043168166485

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Packaging

Carton	1
Package	10
Weight Per each	0.69