



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F40CWX 40W T12 48" 41K 87cri

Sylvania-Ledvance

Catalog Number	F40CWX
Manufacturer	Sylvania-Ledvance
Description	40W, T12 Rapid Start Fluorescent Lamp, Deluxe Cool White Phosphor, 4100K Color Temperature, 87 Cri. 20000 Avg Rated Life At 3 HRS/Start, 28800 Avg Rated Life At 12 HRS/Start. Vivid Color: High Cri Lamps For Color Critical Applications.
Weight per unit	0.6700 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Medium Bipin
Lamp Type	RAPID START
lumens	2150 Initial Lumens at 25 Degrees C
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	40

Material, Color, and Finish

color rendering index (cri)	87
color temperature	4100

Descriptions

Description	40W T12 48" 41K 87CRI
extra long description	SYL F40CWX/24441 F40CWX 30/CS 1/SKU
Long Description	40W, T12 rapid start fluorescent lamp, Deluxe Cool White phosphor, 4100K color temperature, 87 CRI. 20000 Avg rated life at 3 hrs/start, 28800 Avg rated life at 12 hrs/start. VIVID Color: High CRI lamps for color critical applications.
Special Features	COOL WHITE

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135244414
Manufacturers Part Number	F40CWX/24441
UPC	046135244414

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	30
Weight Per each	0.67

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------