



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F40DSGN50 40W T12 48" 5000K 90 Cri Bi-Pin Fluorescent

Sylvania-Ledvance

Catalog Number	F40DSGN50
Manufacturer	Sylvania-Ledvance
Description	40W, T12 Rapid Start Fluorescent Lamp, DSGN 50 Phosphor, 5000K Color Temperature, 90 Cri. 20000 Avg Rated Life At 3 HRS/Start, 28800 Avg Rated Life At 12 HRS/Start. Vivid Color: High Cri Lamps For Color Critical Applications.
Weight per unit	0.6500 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
average life	20000
Base	Medium Bipin
bulb type	T12
Lamp Type	RAPID START
lumens	2200
Shape	T12
start type	RAPID START/PREHEAT
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	40

Material, Color, and Finish

color rendering index (cri)	90
color temperature	5000
Finish	Phosphor Coated

Dimensions and Weight

Diameter	1.5 in
Length	47.78

Descriptions

Description	40W T12 48" 5000K 90 CRI BI-PIN FLUORESCENT
extra long description	SYL F40DSGN50/24683 F40DSGN50 30/CS
Long Description	40W, T12 rapid start fluorescent lamp, DSGN 50 phosphor, 5000K color temperature, 90 CRI. 20000 Avg rated life at 3 hrs/start, 28800 Avg rated life at 12 hrs/start. VIVID Color: High CRI lamps for color critical applications.
Product Type	F40DSGN50 30/CS 1/Sku



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135246838
Manufacturers Part Number	F40DSGN50/24683
UPC	046135246838

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	30
Weight Per each	0.65

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------