



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F40DXECO 40W T12 48" 6500K 90CRI Bi Pin Fluorescent Lamp

Ge By Current Lamps

Catalog Number	F40DXECO
Manufacturer	Ge By Current Lamps
Description	Fluorescent Lamp, G13 Medium Bi-Pin Base, T12 Bulb Shape, 90, 20000 H Average Life, 6500 K, 40 W, 2250 LM Brightness (Lumens), Soda Lime Housing Material, 1.5 In Diameter, 48.0 In Length, Rapid, +10 °C Operating Temperature, 0.67 LB/Ea
Weight per unit	0.6700 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

Base	Medium Bi-Pin (G13)
lumens	2050.0
Wattage	40.0

Material, Color, and Finish

color rendering index (cri)	90.0
-----------------------------	------

Dimensions and Weight

Diameter	1.5
Length	48.0

Descriptions

Description	40W T12 48" 6500K 90CRI BI PIN FLUORESCENT LAMP
extra long description	GEL F40DX/ECO 80097 FLUORESCENT F40

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168800976
UPC	043168800976

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Packaging

Carton	1
Package	30
Weight Per each	0.67