Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F40DXEC0 40W T12 48" 6500K 90CRI Bi Pin Fluorescent Lamp

Ge By Current Lamps

Catalog Number	F40DXEC0
Manufacturer	Ge By Current Lamps
Description	Fluorescent Lamp, G13 Medium Bi-Pin Base, T12 Bulb Shape, 90, 20000 H Average Life, 6500 K, 40 W, 2250 LM Brightness (Lumens), Soda Lime Housing Material, 1.5 In Diameter, 48.0 In Length, Rapid, +10 °C Operating Temperature, 0.67 LB/Ea
Weight per unit	0.6700 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

Base	Medium Bi-Pin (G13)
lumens	2050
Wattage	40

Material, Color, and Finish

color rendering index (cri)	90.0

Dimensions and Weight

Diameter	1.5
Length	48

Descriptions

Description	40W T12 48" 6500K 90CRI BI PIN FLUORESCENT LAMP
extra long description	GEL F40DX/ECO 80097 FLUORESCENT F40

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168800976
UPC	043168800976

Taxonomies, Classifications, and Categories

Category Description	Fluorescent

Packaging

Carton	1
Package	30
Weight Per each	0.67