



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## F42T12CWHO \*Delisted\* 55W T12 Ho Cool White

*Sylvania-Ledvance*

Catalog Number	F42T12CWHO
Manufacturer	Sylvania-Ledvance
Description	OBS25342 55W, 42" Mol, T12 Ho (800 Ma) Rapid Start Fluorescent Lamp, Cool Whitephosphor, 4200K Color Temperature, 60 Cri
Weight per unit	0.6200 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

amperage rating	Ballast Dependent
average life	9000
Base	Recessed Double Contact
lumens	3400 Initial Lumens at 25 Degrees C
Shape	T12
start type	Rapid Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	55

### Material, Color, and Finish

color rendering index (cri)	60
color temperature	4200
Finish	Phosphor Coated

### Dimensions and Weight

Diameter	1.5 in
----------	--------

### Descriptions

Description	*DELISTED* 55W T12 HO COOL WHITE
extra long description	SYL F42T12/CW/HO/25342 F42T12CWHO 3
Long Description	OBS25342 55W, 42" MOL, T12 HO (800 mA) rapid start fluorescent lamp, Cool Whitephosphor, 4200K color temperature, 60 CRI
Product Type	F42T12CWHO 30/CS 1/Sku
Special Features	COOL WHITE

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135253423
Manufacturers Part Number	F42T12/CW/HO/25342
UPC	046135253423



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description Fluorescent

Type FLUORESCENT

## Packaging

Carton 1

Package 30

Weight Per each 0.62

## Uses, Certifications, and Standards

Application Commercial/Residential