



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F44L60 4X4X60 N12 STRT SCT CLMP HC *Hoffman Enclosures, Inc.*

Catalog Number	F44L60
Manufacturer	Hoffman Enclosures, Inc.
Description	Straight Section Lay-In Hinged Cover Type 12, 4.00X4.00X60.00, Gray, Steel
Weight per unit	27.0 (lbs/each)
Product Category	20101115153159

Features

ip rating	IP54
Material	MILD STEEL

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Galvanized

Dimensions and Weight

Height	4
Width	4

Descriptions

Description	4X4X60 N12 STRT SCT CLMP HC
extra long description	NVENT HOF F44L60 60.00in Straight S
Features	Lay-in NEMA Type 12 Wireway fittings are used primarily in industrial applications to protect wiring against exposure to oil and other contaminants. This gasketed wireway features quick-release latches for easy access and an opening on one side so wires and cables can be laid in along the entire run without pulling.
Long Description	Straight Section Lay-in Hinged Cover Type 12, 4.00x4.00x60.00, Gray, Steel
Product Type	60.00IN Straight Section

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510182908
Manufacturers Part Number	F44L60
UPC	783510182908

Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Straight Section



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	27

Uses, Certifications, and Standards

Application	Power Distribution
nema rating	12 Indoor, dust-resistant