



GE
Lighting

61360 - GE Ecolux® Starcoat® T5

F54T5/835ECO/PRO

☞ Passes TCLP, which can lower disposal costs.

GENERAL CHARACTERISTICS

Base Description	Miniature Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	2.5 mg
Rated Life Rapid Start - Hrs	17000 h @ 3 h 20000 h @ 12 h
Starting Temp (MIN) C-degrees	-20 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	17000 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	G5
Bulb Shape	T5

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	3900 lm
Color Rendering Index-CRI	85

PRODUCT INFORMATION

Product Code	61360
Description	F54T5/835ECO/PRO
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168613606
Standard Package GTIN	10043168613603
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168613606

DIMENSIONS

Diameter	0.62 in
Face to End of Opposing Pin (B) <Max>	45.52 in
Face to End of Opposing Pin (B) <Min>	45.42 in
Nominal Length	45.2 in

ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Open Circuit Voltage (rapid start) Min @ Temperature	520.00 V @ 10 °C
Cathode Resistance Ratio - Rh/Rc (MIN)	4.250
Cathode Resistance Ratio - Rh/Rc (MAX)	6.500
Rated power (Watts)	54 W



GE
Lighting

61360 - GE Ecolux® Starcoat® T5

F54T5/835ECO/PRO

☞ Passes TCLP, which can lower disposal costs.

GENERAL CHARACTERISTICS

Base Description	Miniature Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	2.5 mg
Rated Life Rapid Start - Hrs	17000 h @ 3 h 20000 h @ 12 h
Starting Temp (MIN) C-degrees	-20 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	17000 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	G5
Bulb Shape	T5

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	3900 lm
Color Rendering Index-CRI	85

PRODUCT INFORMATION

Product Code	61360
Description	F54T5/835ECO/PRO
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168613606
Standard Package GTIN	10043168613603
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168613606

DIMENSIONS

Diameter	0.62 in
Face to End of Opposing Pin (B) <Max>	45.52 in
Face to End of Opposing Pin (B) <Min>	45.42 in
Nominal Length	45.2 in

ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Open Circuit Voltage (rapid start) Min @ Temperature	520.00 V @ 10 °C
Cathode Resistance Ratio - Rh/Rc (MIN)	4.250
Cathode Resistance Ratio - Rh/Rc (MAX)	6.500
Rated power (Watts)	54 W