



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F66G24WK 6X6X24 N1 HC STRT SCT

Hoffman Enclosures, Inc.

Catalog Number	F66G24WK
Manufacturer	Hoffman Enclosures, Inc.
Description	Lay-In Wireway, Gray, Polyester Powder Paint, Steel, Hinged Cover, 6 In Overall Height, 24 In Overall Length, 6 In Overall Width, 46 LB
Weight per unit	46.0 (lbs/each)
Product Category	Nema Type 1 Wireway & Fittings

Features

ip rating	IP30
-----------	------

Material, Color, and Finish

Color Code	ANSI 61
Style	Liftoff Cover with Knockouts

Dimensions and Weight

Height	6
Width	6

Descriptions

Description	6X6X24 N1 HC STRT SCT
extra long description	NVENT HOF F66G24WK 24.00in Straight
Features	Lay-in Hinged-Cover Type 1 Straight Sections are used for enclosing wire and cable in wireway runs. Sections are completely open on one side so wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system. Sections are available in lengths from 12 inch to 120 inch, with or without knockouts.

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510529604
UPC	783510529604

Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Straight Section

Packaging

Carton	1
Weight Per each	46



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Power Distribution
nema rating	1 Indoor, electrical protection