ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F72T12CWH0 85W T12 72" Cool White High Output 62 Cri R17D

Sylvania-Ledvance

Catalog Number	F72T12CWH0
Manufacturer	Sylvania-Ledvance
Description	85W, 72"Mol, T12 Ho (800 Ma) Rapid Start Fluorescent Lamp, Cool Whitephosphor, 4200K Color Temperature, 60 Cri
Weight per unit	1.1 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Recessed Double Contact
bulb type	T12
Lamp Type	RAPID START
lumens	6250 Initial Lumens at 25 Degrees C
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	85

Material, Color, and Finish

color rendering index (cri)	60
color temperature	4200

Descriptions

Description	85W T12 72" COOL WHITE HIGH OUTPUT 62 CRI R17D
extra long description	LDV F72T12/CW/HO/25176 F72T12CWHO 1
Long Description	85W, 72"MOL, T12 HO (800 mA) rapid start fluorescent lamp, Cool Whitephosphor, 4200K color temperature, 60 CRI
Special Features	COOL WHITE

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135251764
Manufacturers Part Number	F72T12/CW/HO/25176
UPC	046135251764

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	15
Weight Per each	1.08

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Commercial/Residential