



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F72T12DH0 85W T12 72" Daylight High Output 76 Cri R17D

Ge By Current Lamps

Catalog Number	F72T12DH0
Manufacturer	Ge By Current Lamps
Description	Fluorescent Lamp, Recessed Double Contact R17D Base, T12 Bulb Shape, 75, 12000 H Average Life, 6500 K, 85 W, 5350 LM Brightness (Lumens), Soda Lime Housing Material, 1.5 In Diameter, 72.0 In Length, Rapid, -29 °C Operating Temperature, 1.35 LB/Ea
Weight per unit	1.4 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

Base	Recessed Double Contact (R17d)
lumens	5350.0
Wattage	85.0

Material, Color, and Finish

color rendering index (cri)	75.0
-----------------------------	------

Dimensions and Weight

Diameter	1.5
----------	-----

Descriptions

Description	85W T12 72" DAYLIGHT HIGH OUTPUT 76 CRI R17D
extra long description	GEL F72T12D/HO-15PK 13699 FLUORES

Manufacturer Information

Brand	GE Current, a Daintree company
GTIN	00043168136990
Manufacturers Part Number	F72T12D/HO 15PK
UPC	043168136990

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Packaging

Carton	1
Package	15
Weight Per each	1.35