



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F84T12CWHO 100W T12 84" Cool White High Output 62 Cri R17D

Sylvania-Ledvance

Catalog Number	F84T12CWHO
Manufacturer	Sylvania-Ledvance
Description	100W, 84" Mol, T12 Ho (800 Ma) Rapid Start Fluorescent Lamp, Cool Whitephosphor, 4200K Color Temperature, 60 Cri
Weight per unit	1.3 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Recessed Double Contact
lumens	7550 Initial Lumens at 25 Degrees C
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	100

Material, Color, and Finish

color rendering index (cri)	60
color temperature	4200

Descriptions

Description	100W T12 84" COOL WHITE HIGH OUTPUT 62 CRI R17D
extra long description	SYL F84T12/CW/HO/25384 F84T12CWHO 1
Long Description	100W, 84" MOL, T12 HO (800 mA) rapid start fluorescent lamp, Cool Whitephosphor, 4200K color temperature, 60 CRI
Special Features	COOL WHITE

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135253843
Manufacturers Part Number	F84T12/CW/HO/25384
UPC	046135253843

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	15
Weight Per each	1.26

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------