



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F88G72 8X8X72 N1 HC STRT SCT

Hoffman Enclosures, Inc.

Catalog Number	F88G72
Manufacturer	Hoffman Enclosures, Inc.
Description	Straight Section Lay-In Hinged-Cover Type 1 No Kos, 8X8X72, Gray, Steel
Weight per unit	51.0 (lbs/each)
Product Category	Nema Type 1 Wireway & Fittings

Features

ip rating	IP30
Knockouts	NO
Material	MILD STEEL

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Powder Coated
Style	Liftoff Cover no Knockouts

Dimensions and Weight

Height	8
Width	8

Descriptions

Description	8X8X72 N1 HC STRT SCT
extra long description	NVENT HOF F88G72 72.00in Straight S
Features	Lay-in Hinged-Cover Type 1 Straight Sections are used for enclosing wire and cable in wireway runs. Sections are completely open on one side so wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system. Sections are available in lengths from 12 inch to 120 inch, with or without knockouts.
Long Description	Straight Section Lay-in Hinged-Cover Type 1 no KOs, 8x8x72, Gray, Steel
Product Type	72.00IN Straight Section

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510517700
Manufacturers Part Number	F88G72
UPC	783510517700



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description STEEL WIRE WAY JUNCTION BOXES

Type Straight Section

Packaging

Carton 1

Weight Per each 51

Uses, Certifications, and Standards

Application Power Distribution

nema rating 1 Indoor, electrical protection