



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F96T12CWX 75W T12 96" 4100K CW 87 Cri *Sylvania-Ledvance*

Catalog Number	F96T12CWX
Manufacturer	Sylvania-Ledvance
Description	75W, 96 Inch Mol, T12 Instant Start Slimline Fluorescent Lamp, Deluxe Cool White Phosphor, 4100K Color Temperature, 87 Cri. Vivid Color: High Cri Lamps For Color Critical Applications.
Weight per unit	1.4 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Single Pin
Lamp Type	INSTANT START
lumens	4400 Initial Lumens at 25 Degrees C
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	75

Material, Color, and Finish

color rendering index (cri)	87
color temperature	4100

Descriptions

Description	75W T12 96" 4100K CW 87 CRI
extra long description	SYL F96T12CWX/29478 F96T12CWX 15/CS
Long Description	75W, 96 inch MOL, T12 instant start Slimline fluorescent lamp, Deluxe Cool White phosphor, 4100K color temperature, 87 CRI. VIVID Color: High CRI lamps for color critical applications.
Special Features	COOL WHITE

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135294785
Manufacturers Part Number	F96T12/CWX/29478
UPC	046135294785

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	15
Weight Per each	1.4333

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------