



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## F96T12CWSSUPC Lamp F96T12/CWX/SS/Upc *Sylvania-Ledvance*

Catalog Number	F96T12CWSSUPC
Manufacturer	Sylvania-Ledvance
Description	60W, 96 Inch Mol, T12 Instant Start Slimline Super Saver Fluorescent Lamp, Cool White Deluxe Phosphor, 4100K Color Temperature, 87 Cri, Upc Code. Vivid Color: High Cri Lamps For Color Critical Applications
Weight per unit	1.4 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

amperage rating	Ballast Dependent
Base	Single Pin
bulb type	T12
Lamp Type	INSTANT START
lumens	3850
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	60

### Material, Color, and Finish

color rendering index (cri)	87
color temperature	4100

### Descriptions

Description	LAMP F96T12/CWX/SS/UPC
extra long description	SYL F96T12CWSSUPC/23503 F96T12CWXS
Long Description	60W, 96 inch MOL, T12 instant start Slimline SUPER SAVER fluorescent lamp, Cool White Deluxe phosphor, 4100K color temperature, 87 CRI, UPC code. VIVID Color: High CRI lamps for color critical applications

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135235030
Manufacturers Part Number	23503
UPC	046135235030



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

## Packaging

Carton	1
Package	15
Weight Per each	1.43