



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## F96T12DH0COLD 115W T12 96" Daylight High Output Cold Temp 76 Cri

*Sylvania-Ledvance*

Catalog Number	F96T12DH0COLD
Manufacturer	Sylvania-Ledvance
Description	110W, 96"Mol, T12 Ho (800 Ma) Rapid Start Fluorescent Lamp, Daylightphosphor, 6500K Color Temperature, 73 Cri, Labeled For Cold Temperature Applications.
Weight per unit	1.4 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

amperage rating	Ballast Dependent
Base	Recessed Double Contact
lumens	7600 Initial Lumens at 25 Degrees C
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent

### Material, Color, and Finish

color rendering index (cri)	76
color temperature	6500

### Descriptions

Description	115W T12 96" DAYLIGHT HIGH OUTPUT COLD TEMP 76 CRI
extra long description	SYL F96T12DHOCOLDTEMP/25135 F96T12D
Long Description	110W, 96"MOL, T12 HO (800 mA) rapid start fluorescent lamp, Daylightphosphor, 6500K color temperature, 73 CRI, labeled for cold temperature applications.

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135251351
Manufacturers Part Number	F96T12/D/HO/COLD-TEMP/25135
UPC	046135251351

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

### Packaging

Carton	1
Package	15
Weight Per each	1.41

### Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------