




GE
Lighting

68870 - F96T8/XL/SPX41/2

F96T8/XL/SPX41/2



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight
	Linear
Bulb	T8
Base	Single Pin (Fa8)
Rated Life (NOM)	24000.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	10.0 °C
Mercury Content (NOM)	90.0 mg
Picograms of Mercury (NOM)	663.7168 pg
Primary Application	Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	5950.0
Mean Lumens (NOM)	5650.0
Nominal Initial Lumens per Watt (NOM)	100.8475
Color Temperature (NOM)	4100.0 K
Color Rendering Index (CRI) (NOM)	85.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	59.0
---------------	------

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	96.000 in(2438.4 mm)
Nominal Length (NOM)	96.000 in(2438.4 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

PRODUCT INFORMATION


Product Code	68870
Description	F96T8/XL/SPX41/2
Standard Package	Case
Standard Package GTIN	10043168688700
Standard Package Quantity	24
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	24
UPC	043168688703



GE
Lighting

68870 - F96T8/XL/SPX41/2

F96T8/XL/SPX41/2



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight
	Linear
Bulb	T8
Base	Single Pin (Fa8)
Rated Life (NOM)	24000.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	10.0 °C
Mercury Content (NOM)	90.0 mg
Picograms of Mercury (NOM)	663.7168 pg
Primary Application	Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	5950.0
Mean Lumens (NOM)	5650.0
Nominal Initial Lumens per Watt (NOM)	100.8475
Color Temperature (NOM)	4100.0 K
Color Rendering Index (CRI) (NOM)	85.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	59.0
---------------	------

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	96.000 in(2438.4 mm)
Nominal Length (NOM)	96.000 in(2438.4 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

PRODUCT INFORMATION

Product Code	68870
Description	F96T8/XL/SPX41/2
Standard Package	Case
Standard Package GTIN	10043168688700
Standard Package Quantity	24
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	24
UPC	043168688703