

Eaton FAZ-C50/3-NA

Catalog Number: FAZ-C50/3-NA

Eaton FAZ branch protector, UL 489 Industrial miniature circuit breaker - supplementary protector, Medium levels of inrush current are expected, 50 A, 10 kAIC, Three-pole, 240 V, 5-10X /n, 50-60 Hz, Screw terminals, C Curve



Photo is representative

General specifications

Product Name	Catalog Number
Eaton FAZ branch protector	FAZ-C50/3-NA
UPC	Product Length/Depth
786689240813	2.1 in
Product Height	Product Width
3 in	4.1 in
Product Weight	Warranty
0.75 lb	1 year
Certifications	
UL 489	

Physical Attributes

Number of poles

Three-pole

Terminals

Screw

Type

UL 489 Industrial miniature circuit breaker - supplementary protector

Performance Ratings

Amperage Rating

50 A

Circuit protection

C curve

Frequency rating

50-60 Hz

Interrupt rating

10 kAIC

Trip Type

5-10X /n

Voltage rating

277/480V

Miscellaneous

Application

Suitable for applications where medium levels of inrush current are expected

Resources

Catalogs

[UL 489 DIN rail miniature circuit breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - FAZ-C50/3-NA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton FAZ-C50/3-NA

Catalog Number: FAZ-C50/3-NA

Eaton FAZ branch protector, UL 489 Industrial miniature circuit breaker - supplementary protector, Medium levels of inrush current are expected, 50 A, 10 kAIC, Three-pole, 240 V, 5-10X /n, 50-60 Hz, Screw terminals, C Curve



Photo is representative

General specifications

Product Name	Catalog Number
Eaton FAZ branch protector	FAZ-C50/3-NA
UPC	Product Length/Depth
786689240813	2.1 in
Product Height	Product Width
3 in	4.1 in
Product Weight	Warranty
0.75 lb	1 year
Certifications	
UL 489	

Physical Attributes

Number of poles

Three-pole

Terminals

Screw

Type

UL 489 Industrial miniature circuit breaker - supplementary protector

Performance Ratings

Amperage Rating

50 A

Circuit protection

C curve

Frequency rating

50-60 Hz

Interrupt rating

10 kAIC

Trip Type

5-10X /n

Voltage rating

277/480V

Miscellaneous

Application

Suitable for applications where medium levels of inrush current are expected

Resources

Catalogs

[UL 489 DIN rail miniature circuit breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - FAZ-C50/3-NA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)