



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FB031841 31W T8 22.5" 1 5/8" Leg Spacing 4100K 82 Cri

Sylvania-Ledvance

Catalog Number	FB031841
Manufacturer	Sylvania-Ledvance
Description	31W, 22.5" Mol, T8 Octron Curvalume Fluorescent Lamp, 1 5/8" Leg Spacing, 4100K Color Temperature Rare Earth Phosphor, 82 Cri, Suitable For Is or RS Operation
Weight per unit	0.7000 (lbs/each)
Product Category	Shape Lamps

Features

amperage rating	Ballast Dependent
average life	20000
Base	Medium Bipin
bulb type	T8
Lamp Type	RS-CURVALUME
Shape	T8
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	31

Material, Color, and Finish

color rendering index (cri)	82
color temperature	4100
Finish	Phosphor Coated

Dimensions and Weight

Diameter	1
----------	---

Descriptions

Description	31W T8 22.5" 1 5/8" LEG SPACING 4100K 82 CRI
extra long description	SYL FBO31/841/21879 FBO31841 15/CS
Long Description	31W, 22.5" MOL, T8 OCTRON Curvalume fluorescent lamp, 1 5/8" leg spacing, 4100K color temperature rare earth phosphor, 82 CRI, suitable for IS or RS operation
Product Type	FBO31841 15/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135218798
Manufacturers Part Number	FBO31/841/21879
UPC	046135218798



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description Fluorescent

Type FLUORESCENT

Packaging

Carton 1

Package 15

Weight Per each 0.7

Uses, Certifications, and Standards

Application Commercial/Residential