



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FB0327416ECO 32W T8 22.5" 6" Leg Spacing 4100K 75 Cri Bi-Pin

Sylvania-Ledvance

Catalog Number	FB0327416ECO
Manufacturer	Sylvania-Ledvance
Description	32W, 22.5" Mol, T8 Octron Curvalume Fluorescent Lamp, 6" Leg Spacing, 4100K Color Temperature, Rare Earth Phosphor, 75 Cri, Suitable For Is or RS Operation, Ecologic
Weight per unit	0.6200 (lbs/each)
Product Category	Shape Lamps

Features

amperage rating	Ballast Dependent
Base	Medium Bipin
Lamp Type	CURVALUME
lumens	2750 Initial Lumens at 25 Degrees C
Shape	T8
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	32

Material, Color, and Finish

color rendering index (cri)	75
-----------------------------	----

Dimensions and Weight

Diameter	1
----------	---

Descriptions

Description	32W T8 22.5" 6" LEG SPACING 4100K 75 CRI BI-PIN
extra long description	SYL FBO32/741/6/ECO/22052 FBO327416
Long Description	32W, 22.5" MOL, T8 OCTRON Curvalume fluorescent lamp, 6" leg spacing, 4100K color temperature, rare earth phosphor, 75 CRI, suitable for IS or RS operation, ECOLOGIC

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135220524
Manufacturers Part Number	FBO32/741/6/ECO/22052
UPC	046135220524

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	16
Weight Per each	0.62



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

C78.1-1991
