



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FB0327506ECO 32W T8 22.5" 5K 75CRI 6" Leg Space Is or RS Op

Sylvania-Ledvance

Catalog Number	FB0327506ECO
Manufacturer	Sylvania-Ledvance
Description	32W, 22.5" Mol, T8 Octron Curvalume Fluorescent Lamp, 6" Leg Spacing, 5000K Color Temperature Rare Earth Phosphor, 75 Cri, Suitable For Is or RS Operation, Ecologic
Weight per unit	0.6200 (lbs/each)
Product Category	Shape Lamps

Features

amperage rating	Ballast Dependent
average life	20000
Base	Medium Bipin
bulb type	T8
Lamp Type	RS CURVALUME
lumens	2625 Initial Lumens at 25 Degrees C
Shape	T8
start type	Rapid Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	32

Material, Color, and Finish

color rendering index (cri)	75
color temperature	5000
Finish	Phosphor Coated

Dimensions and Weight

Diameter	1
----------	---

Descriptions

Description	32W T8 22.5" 5K 75CRI 6" LEG SPACE IS OR RS OP
extra long description	SYL FBO32/750/6/ECO/22053 FBO327506
Long Description	32W, 22.5" MOL, T8 OCTRON Curvalume fluorescent lamp, 6" leg spacing, 5000K color temperature rare earth phosphor, 75 CRI, suitable for IS or RS operation, ECOLOGIC
Product Type	FBO327506ECO 16/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135220531
Manufacturers Part Number	FBO32/750/6/ECO/22053
UPC	046135220531



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description Fluorescent

Type FLUORESCENT

Packaging

Carton 1

Package 16

Weight Per each 0.62

Uses, Certifications, and Standards

Application Commercial/Residential