



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FE3224 24' Type Ia CFGD Fiberglass Extension Ladder *Louisville Ladder*

Catalog Number	FE3224
Manufacturer	Louisville Ladder
Description	Louisville Ladder, Fiberglass Material, 300 LB Load Rating, 17.063 In Base Width, 149.5 In (Open Height) Overall Height, 1.5 In Step Depth, 12 FT Section Length, 2 Sections, 21 In Extended Height, 24 Steps, 52 LB
Weight per unit	52.0 (lbs/each)
Product Category	Hand Tools - Ladders

Features

Load Capacity	94414
Step Height	6.25 in

Descriptions

Description	24' TYPE IA CFGD FIBERGLASS EXTENSION LADDER
Special Features	Features: Quicklatch; Steel Swivel Safety Shoe With Metal Shield; Outside Slide Guides; D-Shaped Rungs; Mar-Resistant Rail End Caps; Series: FE3200; Length Each Section: 12 FT; Actual Cubic Ft: 10.200 CU-FT; Rail Depth: 3-1/4 IN; Inside Width: 14-11/16 IN Base X 13-11/16 IN Fly; Outside Width: 17-1/16 IN Base X 16-1/16 IN Fly

Manufacturer Information

Brand	Louisville
GTIN	00728865200051
UPC	728865200051

Taxonomies, Classifications, and Categories

Category Description	LADDERS
Type	Type IA, Two Section

Packaging

Carton	1
Weight Per each	52

Uses, Certifications, and Standards

standard	CSA, ANSI A14.5, OSHA
----------	-----------------------