



GE  
Lighting

94542 - GE CFL 14W T3 Spriral

FLE14HT3/2/841

#### GENERAL CHARACTERISTICS

Base Type	Screw-In
Life in Years	9.1 yr
Rated Life Hours-nominal	10000 h
Base Description	Medium Screw
Product Technology	Compact Fluorescent
Base	E26
Bulb Shape	R30

#### PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	68
Initial Lumens-nominal	950 lm
Color Temperature	4100 K

#### PRODUCT INFORMATION

Product Code	94542
Description	FLE14HT3/2/841
Alternative Unit Of Measure	EACH
Standard Package Quantity	10
Ean UPC	043168945424
Standard Package GTIN	00043168945424
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
Sales Unit	Each
UCC	043168945424
Alternative Unit Of Measure	CASE

#### ELECTRICAL CHARACTERISTICS

Equivalent Incandescent Watts	60 W
Estimated Energy Cost per Year	1.69 \$
Dimming Capability	No
Rated power (Watts)	14 W



GE  
Lighting

94542 - GE CFL 14W T3 Spiral

FLE14HT3/2/841

#### GENERAL CHARACTERISTICS

Base Type	Screw-In
Life in Years	9.1 yr
Rated Life Hours-nominal	10000 h
Base Description	Medium Screw
Product Technology	Compact Fluorescent
Base	E26
Bulb Shape	R30

#### PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	68
Initial Lumens-nominal	950 lm
Color Temperature	4100 K

#### PRODUCT INFORMATION

Product Code	94542
Description	FLE14HT3/2/841
Alternative Unit Of Measure	EACH
Standard Package Quantity	10
Ean UPC	043168945424
Standard Package GTIN	00043168945424
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
Sales Unit	Each
UCC	043168945424
Alternative Unit Of Measure	CASE

#### ELECTRICAL CHARACTERISTICS

Equivalent Incandescent Watts	60 W
Estimated Energy Cost per Year	1.69 \$
Dimming Capability	No
Rated power (Watts)	14 W