





GE  
Lighting

## 89091 - FLE15HT3/2/D/CD

GE energy smart® spiral® CFL 15 watt T3 spiral 1-pack

- \$49 in energy savings over the life of the bulb based on 3 hours per day usage
- 60 watt replacement uses only 15 watts
- Energy Star Qualified
- Estimated yearly energy costs \$1.81 based on 3 hours per day \$0.11 per kWh
- Lasts 9.1 years based on 3 hours per day usage
- Save money and save energy with GE energy smart® spiral® CFL bulbs. GE energy smart® bulbs use 75% less energy than standard incandescents, helping you save money on energy. And, because they last 8 times longer than a standard incandescent, you'll replace these bulbs less often. Use general purpose GE energy smart® spiral® CFL bulbs in common household fixtures like table lamps, floor lamps and bare lamp sockets
- T3 spiral shape with medium base for use in table lamps and enclosed fixtures



### CAUTIONS & WARNINGS

#### Caution

- Lamp may shatter and cause injury if broken
  - Remove and install by grasping only plastic portion of the lamp.

#### Warning

- Risk of Electric Shock
  - Do not open - no user serviceable parts inside.
  - Do not use where directly exposed to water.

### GENERAL CHARACTERISTICS

Lamp Type	Compact Fluorescent - Self-Ballasted
Bulb	T3
Base	Medium Screw (E26)
Bulb Finish	Daylight
Equivalent Wattage (NOM)	60.0 W
Rated Life (NOM)	8000.0 h
Total Harmonic Distortion (THD) (NOM)	145.0 %
Life in Years (NOM)	9.1
Mercury Content (NOM)	3.5 mg
Picograms of Mercury (NOM)	592.8 pg
Primary Application	Standard;Facilities;Retail Display;Hospitality;Office;Restaurant

### PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	900.0
Mean Lumens (NOM)	738.0
Nominal Initial Lumens per Watt (NOM)	60.0
Color Temperature (NOM)	6500.0 K
Color Rendering Index (CRI) (NOM)	82.0

### ELECTRICAL CHARACTERISTICS

Wattage (NOM)	15.0
Input Voltage (NOM)	120.0 V
Estimated Energy Cost per Year (NOM)	1.81
Input Current (NOM)	0.23 A
Power Factor (NOM)	0.6

### DIMENSIONS

Maximum Overall Length (MOL) (NOM)	4.800 in(121.9 mm)
Nominal Length (NOM)	4.800 in(121.9 mm)

### PRODUCT INFORMATION

Product Code	89091
Description	FLE15HT3/2/D/CD
Standard Package	Case
Standard Package GTIN	10043168890912
Standard Package Quantity	3
Sales Unit	Blister
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	3
UPC	043168890915