








GE  
Lighting

**80894 - FLE26/2/R40XL827**

GE Floodlight Soft White R40 - Facilities; Retail Display; Hospitality; Office; Restaurant

a product of  
**ecomagination**

-  High Color Rendering
-  cUL Listed
-  Energy Savings
-  UL Listed



**GENERAL CHARACTERISTICS**

Lamp Type	Compact Fluorescent - Self-Ballasted
Bulb	R40
Base	Medium Screw (E26)
Equivalent Wattage	90.0 W
Rated Life	10000.0 hrs
Starting Temperature (MIN)	-15.0 °C
LEED-EB MR Credit	269 picograms Hg per mean lumen hour
Primary Application	Indoor Floodlight;Facilities;Retail Display;Hospitality;Office;Restaurant

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens	1300.0
Mean Lumens	1040.0
Nominal Initial Lumens per Watt	50
Color Temperature	2700.0 K
Color Rendering Index (CRI)	82.0

**ELECTRICAL CHARACTERISTICS**

Wattage	26.0
Input Voltage	120.0 V

**DIMENSIONS**

Maximum Overall Length (MOL)	6.5000 in(165.1 mm)
Nominal Length	6.500 in(165.1 mm)
Bulb Diameter (DIA)	5.000 in(127.0 mm)

**PRODUCT INFORMATION**

Product Code	80894
Description	FLE26/2/R40XL827
Standard Package	Case
Standard Package GTIN	10043168808948
Standard Package Quantity	6
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
UPC	043168808941

**CAUTIONS & WARNINGS**

**Warning**

- Risk of Electric Shock
  - Do not open - no user serviceable parts inside.
  - Do not use where directly exposed to water or outdoors without an enclosed fixture.








GE  
Lighting

**80894 - FLE26/2/R40XL827**

GE Floodlight Soft White R40 - Facilities; Retail Display; Hospitality; Office; Restaurant

a product of  
**ecomagination**

-  High Color Rendering
-  cUL Listed
-  Energy Savings
-  UL Listed



**GENERAL CHARACTERISTICS**

Lamp Type	Compact Fluorescent - Self-Ballasted
Bulb	R40
Base	Medium Screw (E26)
Equivalent Wattage	90.0 W
Rated Life	10000.0 hrs
Starting Temperature (MIN)	-15.0 °C
LEED-EB MR Credit	269 picograms Hg per mean lumen hour
Primary Application	Indoor Floodlight;Facilities;Retail Display;Hospitality;Office;Restaurant

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens	1300.0
Mean Lumens	1040.0
Nominal Initial Lumens per Watt	50
Color Temperature	2700.0 K
Color Rendering Index (CRI)	82.0

**ELECTRICAL CHARACTERISTICS**

Wattage	26.0
Input Voltage	120.0 V

**DIMENSIONS**

Maximum Overall Length (MOL)	6.5000 in(165.1 mm)
Nominal Length	6.500 in(165.1 mm)
Bulb Diameter (DIA)	5.000 in(127.0 mm)

**PRODUCT INFORMATION**

Product Code	80894
Description	FLE26/2/R40XL827
Standard Package	Case
Standard Package GTIN	10043168808948
Standard Package Quantity	6
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
UPC	043168808941

**CAUTIONS & WARNINGS**

**Warning**

- Risk of Electric Shock
  - Do not open - no user serviceable parts inside.
  - Do not use where directly exposed to water or outdoors without an enclosed fixture.