



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## FLE70ESP8 70" Esp Damp Rated Fleming Ceiling Fan

*Craftmade International I*

Catalog Number	FLE70ESP8
Manufacturer	Craftmade International I
Description	Engineered For Large Indoor or Outdoor Spaces, The Captivating, Contemporary, Industrial Style and Energy Saving, 6-Speed, Reversible DC Motor Of The Indoor/Outdoor Fleming 70" Ceiling Fan Provides A Look and Feel That Delivers Maximum Performance With The Added Convenience Of A Dimmable Integrated Led Light With Optional Cover and Handheld Remote and Wall Controls.
Weight per unit	20.9 (lbs/each)
Product Category	20200605122656

### Features

bulb type	LED
Category	Fans
Safety Rating	Damp
Voltage	120.00 FT

### Material, Color, and Finish

Finish	Bronze/Dark
Style	Transitional

### Descriptions

Description	70" ESP DAMP RATED FLEMING CEILING FAN
Long Description	Engineered for large indoor or outdoor spaces, the captivating, contemporary, industrial style and energy saving, 6-speed, reversible DC motor of the indoor/outdoor Fleming 70" ceiling fan provides a look and feel that delivers maximum performance with the added convenience of a dimmable integrated LED light with optional cover and handheld remote and wall controls.
Product Type	70"Ceiling Fan

### Manufacturer Information

Brand	CRAFTMADE
GTIN	00647881211226
Manufacturers Part Number	FLE70ESP8
UPC	647881211226

### Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Damp Location

### Packaging

Carton	1
Weight Per each	20.94