







Base	Watts	Nominal Length (in)	Order Code	Description	Case/Std. Pkg Qty	Volts	Initial Lumens	Mean Lumens	Color Temp K	CRI	Min. Start. Temp (°F)	Power Factor	THD	Rated Life (hrs)	Life In Years	Energy Cost \$/Year	ENERGY STAR® Ver. 1.0	Additional Information	Caution Notice	Footnotes	
Self-Ballasted Lamps (continued)																					
Spiral® T2 (continued)																					
	Med	10	3.7	72468	FLE10HT2/6H/CWCD	3	120	580	464	4000K	82	-10	0.5	<85	8000	7.3	\$1.20		T2 Spiral®	GE2000-2709	19,20,21,22
		10	3.5	68518	FLE10HT2D/XL/BX3	4	120	550	440	5000K	82	-10	0.5	<85	12000	11.0	\$1.20	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		10	3.5	62948	FLE10HT2/12H/DCD	6	120	550	440	5000K	82	-10	0.5	<85	12000	11.0	\$1.20	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		10	3.7	72471	FLE10HT2/6H/D/CD	3	120	550	440	6500K	82	-10	0.5	<85	8000	7.3	\$1.20		T2 Spiral®	GE2000-2709	19,20,21,22
	Med	13	3.9	86256	FLE13HT2/2/827	10	120	870	696	2700K	82	-10	0.5	<85	12000	11.0	\$1.57		T2 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		13	3.9	85383	FLE13HT2/2/SW/CD	3	120	870	696	2700K	82	-10	0.6	<85	12000	11.0	\$1.57		T2 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		13	3.9	62949	FLE13HT2/12H/DCD	10	120	850	680	5000K	82	-10	0.5	<85	12000	11.0	\$1.57	★	T2 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22,25
		13	3.9	68505	FLE13HT2SWXL/BX3	4	120	870	696	2700K	82	-10	0.5	<85	12000	11.0	\$1.57	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		13	3.9	68511	FLE13HT2SWXL/BX6	4	120	870	696	2700K	82	-10	0.5	<85	12000	11.0	\$1.57	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		13	3.9	70909	FLE13HT2SWXL/B10	5	120	870	696	2700K	82	-10	0.5	<85	12000	11.0	\$1.57	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		13	3.9	70776	FLE13HT2SWXL/BX4	3	120	870	696	2700K	82	-10	0.5	<85	12000	11.0	\$1.57	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		13	3.9	85390	FLE13HT2/2/SW2PK	3	120	870	696	2700K	82	-10	0.5	<85	12000	11.0	\$1.57	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		13	3.9	72466	FLE13HT2/6H/SWCD	3	120	870	696	2700K	82	-10	0.5	<85	12000	11.0	\$1.57	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		13	3.8	72469	FLE13HT2/6H/CWCD	3	120	870	696	4000K	82	-10	0.5	<85	8000	7.3	\$1.57		T2 Spiral®	GE2000-2709	19,20,21,22
		13	3.9	68519	FLE13HT2D/XL/BX3	4	120	825	660	6500K	82	-10	0.5	<85	12000	11.0	\$1.57	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		13	3.9	70830	FLE13HT2D/XL/BX4	3	120	825	660	6500K	82	-10	0.5	<85	12000	11.0	\$1.57	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		13	3.8	72472	FLE13HT2/6H/D/CD	3	120	825	660	6500K	82	-10	0.5	<85	8000	7.3	\$1.57		T2 Spiral®	GE2000-2709	19,20,21,22
	Med	20	4.1	72880	FLE20HT2/2/XL/CD	3	120	1300	1040	2700K	82	-10	0.6	<85	12000	11.0	\$2.41	★	T2 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22,25
		20	4.1	62951	FLE20HT2/12H/DCD	3	120	1300	1040	5000K	82	-10	0.6	<85	12000	11.0	\$2.41	★	T2 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22,25
		20	4.1	68512	FLE20HT2SWXL/BX6	4	120	1300	1040	2700K	82	-10	0.5	<85	12000	11.0	\$2.41	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		20	4.1	68506	FLE20HT2SWXL/BX3	4	120	1300	1040	2700K	82	-10	0.5	<85	12000	11.0	\$2.41	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
	Med	20	4.1	72875	FLE20HT2/2/XL/2P	3	120	1300	1040	2700K	82	-10	0.5	<85	12000	11.0	\$2.41	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		20	4.1	68520	FLE20HT2D/XL/BX3	4	120	1300	1040	5000K	82	-10	0.5	<85	12000	11.0	\$2.41	★	T2 Spiral®	GE2000-2709	19,20,21,22,25
		23	4.5	72881	FLE26HT2/2/XL/CD	3	120	1600	1280	2700K	82	-15	0.6	<85	12000	11.0	\$2.77		T2 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		23	4.5	68513	FLE23HT2SWXL/BX6	4	120	1600	1280	2700K	82	-15	0.5	<85	12000	11.0	\$2.77		T2 Spiral®	GE2000-2709	19,20,21,22
		23	4.5	68507	FLE23HT2SWXL/BX3	4	120	1600	1280	2700K	82	-15	0.5	<85	12000	11.0	\$2.77		T2 Spiral®	GE2000-2709	19,20,21,22
		23	4.5	72877	FLE23HT2/2/XL/2P	3	120	1600	1280	2700K	82	-15	0.5	<85	12000	11.0	\$2.77		T2 Spiral®	GE2000-2709	19,20,21,22
		26	4.8	62952	FLE26HT2/12H/DCD	3	120	1600	1280	6500K	82	-15	0.6	<85	12000	11.0	\$3.13		T2 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		26	4.8	68521	FLE26HT2D/XL/BX3	4	120	1600	1280	6500K	82	-15	0.5	<85	12000	11.0	\$3.13		T2 Spiral®	GE2000-2709	19,20,21,22
		26	4.8	73633	FLE26HT2/6H/DCD	3	120	1600	1280	6500K	82	-15	0.5	<85	8000	7.3	\$3.13		T2 Spiral®	GE2000-2709	19,20,21,22
	Spiral® T3																				
	Med	9	4.2	42165	FLE9HT3/2/827	10	120	520	416	2700K	82	-15	0.6	<85	10000	9.1	\$1.08	★	T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		9	4.2	42171	FLE9HT3/2/B41	10	120	520	416	4100K	82	-15	0.6	<85	10000	9.1	\$1.08	★	T3 Spiral®	GE2024-7455	1,7,8,9,11,19,20,21,22
		9	4.0	49906	FLE10HT3/2/SW/CD	12	120	520	416	2700K	82	-15	0.6	<85	10000	9.1	\$1.08		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		9	4.0	49907	FLE10HT3/2/SW/CD	12	120	520	416	2700K	82	-15	0.6	<85	10000	9.1	\$1.08		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		9	4.0	49907	FLE10HT3/2/SW/CD	12	120	520	416	2700K	82	-15	0.6	<85	10000	9.1	\$1.08		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		9	4.0	49907	FLE10HT3/2/SW/CD	12	120	520	416	2700K	82	-15	0.6	<85	10000	9.1	\$1.08		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		9	4.0	89082	FLE10HT3/2/D/CD	12	120	500	400	6500K	82	-15	0.6	<85	10000	9.1	\$1.08		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		9	4.0	89082	FLE10HT3/2/D/CD	12	120	500	400	6500K	82	-15	0.6	<85	10000	9.1	\$1.08		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		9	4.0	65670	FLE9HT3/2SW/BX4	3	120	520	416	2700K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
		9	4.0	72931	FLE10HT3/2/SW6PK	4	120	520	416	2700K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
		9	4.0	76991	FLE9HT3/2/CB/BX	10	120	520	416	2700K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
		9	4.0	49807	FLE9HT3/2SWCD3PK	3	120	520	416	2700K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
		9	4.0	74196	FLE9HT3/2/SW/BX	10	120	520	416	2700K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
		9	4.0	97688	FLE9HT3/2/SWBX3	4	120	520	416	2700K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
		9	4.0	74197	FLE9HT3/2/BX/2P	6	120	520	416	2700K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
		9	4.0	73156	FLE9HT3/2/SW5PK	5	120	520	416	2700K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
		9	4.0	67448	FLE9HT3/41BX4HH	3	120	550	440	4100K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
		9	4.0	67444	FLE9HT3/41BX2HH	6	120	550	440	4100K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
		9	4.0	64004	FLE9HT3/2DBX2/6	6	120	500	400	6500K	82	-15	0.5	<85	10000	9.1	\$1.08		T3 Spiral®	GE2024-7455	19,20,21,22
	Med	10	4.4	80936	FLE10HT3/2/XL	10	120	550	440	2700K	80	-15	0.6	<85	12000	11.0	\$1.20		T3 Spiral®	GE2000-0948	1,7,8,9,10,19,20,21,22
		10	4.4	69658	FLE10HT3XXLL/5BX	3	120	500	400	2700K	82	-10	0.5	<85	15000	13.7	\$1.20		T3 Spiral®	GE2000-2709	19,20,21,22
		10	4.4	69654	FLE10HT3XXLL/2BX	3	120	500	400	2700K	82	-10	0.5	<85	15000						