

HID Flood Lights

250 – 1000W PS | HPS

FEATURES

- Die Cast Aluminum Housing
- Hinged Face Frame
- Tempered Glass Lens
- High Output Reflector
- UL Listed for Ground Mounting
- Pre-wired with Cord

FLL Series

16" Die Cast Flood Light



ORDERING INFORMATION

| CATALOG # | DESCRIPTION | VOLTS | BALLAST TYPE | LAMP |
|--------------------|-------------|-------|--------------|---------|
| Pulse Start | | | | |
| FLL-250PQPK | 250 watt PS | Quad | CWA | MS250/H |
| FLL-400PQPK | 400 watt PS | Quad | CWA | MS400/H |
| FLL-400P5PK | 400 watt PS | 5-Tap | CWA | MS400/H |

For Slipfitter Add Suffix "S"

FEATURES

- Die Cast Aluminum Housing
- Hinged Face Frame
- Tempered Glass Lens
- High Output Reflector
- UL Listed for Ground Mounting
- Pre-wired with Cord

FLLX Series

23" Die Cast Flood Light



ORDERING INFORMATION

| CATALOG # | DESCRIPTION | VOLTS | BALLAST TYPE | LAMP |
|-----------------------------|-------------------------------------|-------|--------------|----------|
| Pulse Start | | | | |
| FLLX-1000P5T | 1000 watt Pulse Start w/ Trunion | 5-Tap | CWA | No lamp |
| FLLX-1000P5S | 1000 watt Pulse Start w/ Slipfitter | 5-Tap | CWA | No lamp |
| High Pressure Sodium | | | | |
| FLLX-1000HQPKT | 1000 watt HPS w/ Trunion | Quad | CWA | C1000S52 |
| FLLX-1000HQPKS | 1000 watt HPS w/ Slipfitter | Quad | CWA | C1000S52 |

Accessories

Mounting

ORDERING INFORMATION

| CATALOG # | DESCRIPTION | FINISH |
|-----------|--|--------|
| FP19BL | 17 1/2" Pedestal w/ 1 Piece Molded Cap; 1/2" Threaded NPS for Fixture Mounting | Black |
| 280-032 | Adjustable Post Top Fitter 1/2" Threaded Apertures | Bronze |
| 320-035BZ | Slipfitter for FLDX | Bronze |
| 280-016-1 | Slipfitter for FLL | Bronze |

Face Frame Assemblies

ORDERING INFORMATION

| CATALOG # | DESCRIPTION | FINISH |
|-----------|-------------------------|--------|
| 210-001 | FL Face Frame Assembly | Bronze |
| 210-004 | FLM Face Frame Assembly | Bronze |



HID Flood Lights

250 – 1000W PS | HPS

FEATURES

- Die Cast Aluminum Housing
- Hinged Face Frame
- Tempered Glass Lens
- High Output Reflector
- UL Listed for Ground Mounting
- Pre-wired with Cord

FLL Series

16" Die Cast Flood Light



ORDERING INFORMATION

| CATALOG # | DESCRIPTION | VOLTS | BALLAST TYPE | LAMP |
|--------------------|-------------|-------|--------------|---------|
| Pulse Start | | | | |
| FLL-250PQPK | 250 watt PS | Quad | CWA | MS250/H |
| FLL-400PQPK | 400 watt PS | Quad | CWA | MS400/H |
| FLL-400P5PK | 400 watt PS | 5-Tap | CWA | MS400/H |

For Slipfitter Add Suffix "S"

FEATURES

- Die Cast Aluminum Housing
- Hinged Face Frame
- Tempered Glass Lens
- High Output Reflector
- UL Listed for Ground Mounting
- Pre-wired with Cord

FLLX Series

23" Die Cast Flood Light



ORDERING INFORMATION

| CATALOG # | DESCRIPTION | VOLTS | BALLAST TYPE | LAMP |
|-----------------------------|-------------------------------------|-------|--------------|----------|
| Pulse Start | | | | |
| FLLX-1000P5T | 1000 watt Pulse Start w/ Trunion | 5-Tap | CWA | No lamp |
| FLLX-1000P5S | 1000 watt Pulse Start w/ Slipfitter | 5-Tap | CWA | No lamp |
| High Pressure Sodium | | | | |
| FLLX-1000HQPKT | 1000 watt HPS w/ Trunion | Quad | CWA | C1000S52 |
| FLLX-1000HQPKS | 1000 watt HPS w/ Slipfitter | Quad | CWA | C1000S52 |

Accessories

Mounting

ORDERING INFORMATION

| CATALOG # | DESCRIPTION | FINISH |
|-----------|--|--------|
| FP19BL | 17 1/2" Pedestal w/ 1 Piece Molded Cap; 1/2" Threaded NPS for Fixture Mounting | Black |
| 280-032 | Adjustable Post Top Fitter 1/2" Threaded Apertures | Bronze |
| 320-035BZ | Slipfitter for FLDX | Bronze |
| 280-016-1 | Slipfitter for FLL | Bronze |

Face Frame Assemblies

ORDERING INFORMATION

| CATALOG # | DESCRIPTION | FINISH |
|-----------|-------------------------|--------|
| 210-001 | FL Face Frame Assembly | Bronze |
| 210-004 | FLM Face Frame Assembly | Bronze |

