



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FNM2810 250V TD Midget Fuse

Bussmann Fuses

Catalog Number	FNM2810
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series FNM Fuse, Time-Delay, 2.8 A, Dual, Non-Indicating, Ferrule End X Ferrule End, 100 Aic At 250 Vac, 10 Kaic At 125 Vac, Nickel-Plated Bronze Endcap, Standard, 250 V
Weight per unit	0.2000 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	2-8/10 Amp
class	Supplemental
connection	Ferrule End X Ferrule End
dimensions	1.5000 IN X 0.4100 IN X 0.4100 IN
element	Dual
interrupt rating	100 Amp at 250 Vac, 10000 Amp at 125 Vac
Material	Nickel-plated bronze endcap
media	Yes
Voltage Rating	250 VAC

Dimensions and Weight

Size	13/32 In Diameter X 1-1/2 In Length
------	-------------------------------------

Descriptions

Description	250V TD MIDGET FUSE
extra long description	BUSS FNM-2-8/10 BUSS MIDGET FUSE
Features	Bussmann offers the broadest selection of Supplemental and Midget fuses in both time-delay and fast-acting designs with voltages as high as 600Vac and 600Vdc.
Long Description	Eaton Bussmann series FNM fuse, Time-delay, 2.8 A, Dual, Non-indicating, Ferrule end x ferrule end, 100 AIC at 250 Vac, 10 kAIC at 125 Vac, Nickel-plated bronze endcap, Standard, 250 V
Product Type	Buss Midget Fuse
Special Features	Nickle Plated Brass Endcap

Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712520232
Manufacturers Part Number	FNM-2-8/10
UPC	051712520232



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description MIDGET FUSES

Type FUSE

Packaging

Carton 10

Weight Per each 0.2

Uses, Certifications, and Standards

Application Ind Facilities & Factories - Facility: Safety and Security Systems

standard RoHS Compliant,CE Marked