




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FP14835ECO FP14835ECO Fluor Lamp

Sylvania-Ledvance

Catalog Number	FP14835ECO
Manufacturer	Sylvania-Ledvance
Description	14W, T5 Pentron Fluorescent Lamp, 3500K Color Temperature, Rare Earth Phosphor, 85 Cri, Ecologic
Weight per unit	0.1300 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
average life	20000
Base	Miniature Bipin
bulb type	T5
lumens	1,200
Shape	T5
start type	Programmed Rapid Start
total harmonic distortion	Ballast Dependent
Voltage	230.00 V
Voltage Rating	Ballast Dependent
Wattage	14

Material, Color, and Finish

color rendering index (cri)	85
color temperature	3500
Finish	Phosphor Coated

Dimensions and Weight

Diameter	0.625
----------	-------

Descriptions

Description	FP14835ECO FLUOR LAMP
extra long description	SYL FP14/835/ECO/20908 FP14835ECO 4
Long Description	14W, T5 PENTRON fluorescent lamp, 3500K color temperature, rare earth phosphor, 85 CRI, ECOLOGIC
Product Type	FP14835ECO 40/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135209086
Manufacturers Part Number	FP14/835/ECO/20908
UPC	046135209086



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description Fluorescent

Type FLUORESCENT

Packaging

Carton 1

Package 40

Weight Per each 0.13

Uses, Certifications, and Standards

Application Commercial/Residential