



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FP14841ECO 14W T5 22" 41K 85cri *Sylvania-Ledvance*

Catalog Number	FP14841ECO
Manufacturer	Sylvania-Ledvance
Description	14W, T5 Pentron Fluorescent Lamp, 4100K Color Temperature, Rare Earth Phosphor, 85 Cri, Ecologic
Weight per unit	0.1300 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
average life	20000
Base	Miniature Bipin
Lamp Type	PROGRAMMED RAPID START
lumens	1,200
Shape	T5
start type	Programmed Rapid Start
total harmonic distortion	Ballast Dependent
Voltage	230.00 V
Voltage Rating	Ballast Dependent
Wattage	14

Material, Color, and Finish

color rendering index (cri)	85
color temperature	4100
Finish	Phosphor Coated

Dimensions and Weight

Diameter	0.625
----------	-------

Descriptions

Description	14W T5 22" 41K 85CRI
extra long description	SYL FP14/841/ECO/20914 FP14841ECO 4
Long Description	14W, T5 PENTRON fluorescent lamp, 4100K color temperature, rare earth phosphor, 85 CRI, ECOLOGIC
Product Type	FP14841ECO 40/CS 1/Sku
Special Features	COOL WHITE

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135209147
Manufacturers Part Number	FP14/841/ECO/20914
UPC	046135209147



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description Fluorescent

Type FLUORESCENT

Packaging

Carton 1

Package 40

Weight Per each 0.13

Uses, Certifications, and Standards

Application Commercial/Residential