



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## FP24841HOECO FP24841HOECO Fluor Lamp

*Sylvania-Ledvance*

Catalog Number	FP24841HOECO
Manufacturer	Sylvania-Ledvance
Description	24W, T5 Pentron High Output (Ho) Fluorescent Lamp, 4100K Color Temperature, Rare Earth Phosphor, 85 Cri, Ecologic
Weight per unit	0.1200 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

amperage rating	Ballast Dependent
average life	25000
Base	Miniature Bipin
bulb type	T5
Lamp Type	PROGRAMMED RAPID START
lumens	1,760
Shape	T5
start type	Programmed Rapid Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	24

### Material, Color, and Finish

color rendering index (cri)	85
color temperature	4100
Finish	Phosphor Coated

### Dimensions and Weight

Diameter	0.625
----------	-------

### Descriptions

Description	FP24841HOECO FLUOR LAMP
extra long description	SYL FP24/841/HO/ECO/20931 FP24841HO
Long Description	24W, T5 PENTRON high output (HO) fluorescent lamp, 4100K color temperature, rare earth phosphor, 85 CRI, ECOLOGIC
Product Type	FP24841HOECO 40/CS 1/Sku
Special Features	COOL WHITE

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135209314
Manufacturers Part Number	FP24/841/HO/ECO/20931
UPC	046135209314



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... Fluorescent

Type ..... FLUORESCENT

## Packaging

Carton ..... 1

Package ..... 40

Weight Per each ..... 0.12

## Uses, Certifications, and Standards

Application ..... Commercial/Residential