



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FP28841ECO 28W T5 41K 85 Cri

Sylvania-Ledvance

Catalog Number	FP28841ECO
Manufacturer	Sylvania-Ledvance
Description	28W, T5 Pentron Fluorescent Lamp, 4100K Color Temperature, Rare Earth Phosphor, 85 Cri, Ecologic
Weight per unit	0.2700 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Miniature Bipin
Lamp Type	PROGRAMMED RAPID START
lumens	2600/2900 (Initial), 2418/2697 (Mean)
Shape	T5
start type	Programmed Rapid Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	28

Material, Color, and Finish

color rendering index (cri)	85
color temperature	4100

Descriptions

Description	28W T5 41K 85 CRI
extra long description	SYL FP28/841/ECO/20902 FP28841ECO 4
Long Description	28W, T5 PENTRON fluorescent lamp, 4100K color temperature, rare earth phosphor, 85 CRI, ECOLOGIC

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135209024
Manufacturers Part Number	FP28/841/ECO/20902
UPC	046135209024

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	40
Weight Per each	0.27