




# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **FP30115WHITE4BOX 4'X1-1/2" WH Thnwal Heat Shrink** *Minnesota Mining (3M)*

Catalog Number	FP30115WHITE4BOX
Manufacturer	Minnesota Mining (3M)
Description	Tubing, Heat; White; 600 V; Cable Size 1-1/2 Inch; Thin Wall; Shrink Temperature 212 Deg F; Flexible Polyolefin; Shrink Ratio 2:1; Minimum Expanded Diameter 1.5 Inch; Maximum Recovered Diameter 0.75 Inch; Length 4 FT; Temperature Rating 131 to 275 Deg F
Weight per unit	N/A
Product Category	Insulating Materials

### **Features**

Cable Size	1-1/2 INCH
Material	FLEXIBLE POLYOLEFIN
Maximum Recovered Diameter	0.75 INCH
Minimum Expanded Diameter	1.5 INCH
Shrink Ratio	2:1
Shrink Temperature	212 DEG F
Voltage Rating	600 V
Wall Type	THIN

### **Material, Color, and Finish**

Color	White
-------	-------

### **Dimensions and Weight**

Length	4 ft
Thickness	0.04 INCH



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Additional Information	STANDARD PACKAGE 5 PER CASE
Commodity Description	Markers & Marking Tapes - Insulating Materials
Description	4"X1-1/2" WH THNWAL HEAT SHRINK
extra long description	HEAT; WHITE COLOR; 600 V VOLTAGE RATING; THIN WALL; SHRINK TEMPERATURE 212 DEG F; FLEXIBLE POLYOLEFIN MATERIAL; SHRINK RATIO 2:1; MINIMUM EXPANDED DIAMETER 1.5 INCH; MAXIMUM RECOVERED DIAMETER 0.75 INCH; LENGTH 4 FT LENGTH; THICKNESS 0.04 INCH; TEMPERATURE RATING -55 TO 135 DEG C; APPROVAL UL, CSA; FP-301 MODEL; SIZE 1 1/2 INCH; PACKAGING TYPE BOX
Long Description	TUBING, HEAT; WHITE; 600 V; CABLE SIZE 1-1/2 INCH; THIN WALL; SHRINK TEMPERATURE 212 DEG F; FLEXIBLE POLYOLEFIN; SHRINK RATIO 2:1; MINIMUM EXPANDED DIAMETER 1.5 INCH; MAXIMUM RECOVERED DIAMETER 0.75 INCH; LENGTH 4 FT; TEMPERATURE RATING 131 TO 275 DEG F
Product Type	Heat Shrink Tubing

## Manufacturer Information

Brand	Minnesota Mining (3M)
GTIN	00051135367339
Manufacturers Part Number	FP-301-1.5-WHITE-4-BOX
Model	FP-301
UPC	051135367339

## Taxonomies, Classifications, and Categories

Category Description	HEAT/COLD SHRINK
Type	HEAT

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	1
Package	5
Weight Per each	0

## Uses, Certifications, and Standards

Approval	UL, CSA
Temperature Rating	131 TO 275 DEG F